



Silicone Coated A

Sil Ctd 60W Med 120V A19 CL 2WR

The Philips Family of Silicone Coated A bulbs are the perfect choice in areas where there is concern if a bulb drops or shatters. Since Silicone Coated A bulbs resist breakage or shattering, they are perfect for food serving areas, as well as, standard, industrial rough surface, appliance and sign use.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	A19
Bulb Finish	Clear
Filament Shape	C-9 [Pendant]
Operating Position	Horizontal [Parallel or Horizontal(HOR)]
Main Application	Silicon Coated
Atmosphere	Gas
Estimated Energy Cost/YR	7.23 \$
Life with 3h/day use [years]	3.2 an

• Light Technical Characteristics

Initial lumen	630 Lm
---------------	--------

• Electrical Characteristics

Watts	60 W
Voltage	120 V

• Product Dimensions

Light Center Length L	2.992 in
-----------------------	----------

Max Overall Length (MOL) - C	4.438 (max) in
Diameter D	2.375 in

• Footnotes


Footnotes Incandescent	902 [Exclusive to Philips Lighting Company.]
Footnotes Incandescent	66 [Silicone Coating reduces lumen output from Standard Values less than 3%. (66)]

• Product Data

Product number	149658
Full product name	Sil Ctd 60W Med 120V A19 CL 2WR
Short product name	Sil Ctd 60W Med 120V A19 CL 2WR
Pieces per Sku	1
eop_pck_cfg	60
Skus/Case	60
Bar code on pack	46677258368
Bar code on case	50046677149654
Logistics code(s)	925279936307
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing



A19



E26

E26, A19

Product	C (Max)	D (Norm)
Std 60W E26 120V A19 CL	4.438	2.375



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change