



# Rapid Start T8

F40T8 40W/835 Medium Bi-Pin ALTO 1LP

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Rated Avg. Life [3 hr Start]	20000 hr
Energy Saving	Energy Saving

### • Light Technical Characteristics

Color Code	TL835 [CCT of 3500K]
Color Rendering Index	86 Ra8
Color Designation	TL835
Color Temperature	3500 K
Initial lumen	3775 Lm
Design Mean Lumens	3500 Lm

### • Electrical Characteristics

Watts	40 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	3.5 mg
----------------------	--------

Picogram per Lumen Hour	50 p/LuHr
-------------------------	-----------

### • Product Dimensions

Nominal Length [inch]	60
-----------------------	----


### • Product Data

Product number	368340
Full product name	F40T8 40W/835 Medium Bi-Pin ALTO 1LP
Short product name	F40T8 40W/835 Medium Bi-Pin ALTO 1LP
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677368340
Bar code on case	50046677368345
Logistics code(s)	927870583501
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity


## Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change