



# High Output T12

F30T12 CW HO

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

## Product data

### • General Characteristics

Base	R17d [Recessed Double Contact Bay (RDC Bay-Fluorescent)]
Base Information	Aluminum [Aluminum Base]
Bulb	T12
Rated Avg. Life [3 hr Start]	9000 hr
Energy Saving	Not Applicable

### • Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	2290 Lm
Design Mean Lumens	1900 Lm

### • Electrical Characteristics

Watts	40 W
-------	------

### • Product Dimensions

Nominal Length [inch]	30
-----------------------	----

### • Footnotes

Footnotes Fluorescent/CFL	207 [Approximate initial lumens are for 800 ma. operation. For 1000 ma. operation, lumens are approximately 10% higher and watts approximately 15% higher. (207)]
---------------------------	---

### Footnotes Fluorescent/CFL

214 [Econ-o-watt® lamps are only recommended for use on high power factor lead, indoor ballasts that meet ANSI standards. The lamps are not recommended for use in drafty areas, or locations where the ambient temperature is less than 60°F, except as noted. Also they should not be operated on low power factor ballasts, reduced light or reduced current ballasts, dimming ballasts or emergency system inverter ballasts. (214)]


### • Product Data

Product number	141424
Full product name	F30T12 CW HO
Short product name	F30T12 CW HO
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677141424
Bar code on case	50046677141429
Logistics code(s)	927886203302
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

## Dimensional drawing



T12 Recessed Double Contact  
R17d, T12



T12 Recessed Double Contact  
R17d, T12



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change