



Preheat T8

F18T8 CW 30 1LP

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Aluminum [Aluminum Base]
Bulb	T8
Rated Avg. Life [3 hr Start]	7500 hr

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	1295 Lm
Design Mean Lumens	1070 Lm

• Electrical Characteristics

Watts	18 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	1.9 mg
----------------------	--------

Picogram per Lumen Hour	197 p/LuHr
-------------------------	------------

• Product Dimensions

Nominal Length [inch]	30
-----------------------	----


• Product Data

Product number	236919
Full product name	F18T8 CW 30 1LP
Short product name	F18T8 CW 30 1LP
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677236915
Bar code on case	50046677236910
Logistics code(s)	927875803301
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change