



Preheat T8

F18T8 CW 24 1LP

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

| | |
|------------------------------|---|
| Base | Medium Bi-Pin [Medium Bi-Pin Fluorescent] |
| Base Information | Aluminum [Aluminum Base] |
| Bulb | T8 |
| Rated Avg. Life [3 hr Start] | 7500 hr |

• Light Technical Characteristics

| | |
|-----------------------|------------|
| Color Code | 33 |
| Color Rendering Index | 62 Ra8 |
| Color Designation | Cool White |
| Color Temperature | 4100 K |
| Initial lumen | 1130 Lm |
| Design Mean Lumens | 1035 Lm |

• Electrical Characteristics

| | |
|-------|------|
| Watts | 18 W |
|-------|------|

• Environmental Characteristics

| | |
|----------------------|-------|
| Mercury (Hg) Content | 16 mg |
|----------------------|-------|

| | |
|-------------------------|-------------|
| Picogram per Lumen Hour | 2061 p/LuHr |
|-------------------------|-------------|

• Product Dimensions

| | |
|-----------------------|----|
| Nominal Length [inch] | 24 |
|-----------------------|----|


• Product Data

| | |
|--------------------|-----------------|
| Product number | 236901 |
| Full product name | F18T8 CW 24 1LP |
| Short product name | F18T8 CW 24 1LP |
| Pieces per Sku | 1 |
| eop_pck_cfg | 24 |
| Skus/Case | 24 |
| Bar code on pack | 46677236908 |
| Bar code on case | 50046677236903 |
| Logistics code(s) | 927875903301 |
| eop_net_weight_pp | 0.001 kg |


PHILIPS

sense and simplicity


Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change