



PL-L Long 4-Pin Base

PL-L 50W/841/4P RS 1CT

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

• General Characteristics

System Description	Rapid Start
Base	2G11
Base Information	4P
Avg. Life	10000 hr

• Light Technical Characteristics

Color Code	841 [CCT of 4100K]
Color Rendering Index	82 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Chromaticity Coordinate X	380 -
Chromaticity Coordinate Y	380 -
Initial Lumens	4000 Lm
Luminous Efficacy	80 Lm/W
Lamp EM	
Lumen Maintenance EM 2000h	94 %
Lumen Maintenance EM 5000h	91 %
Lumen Maintenance EM 10000h	91 %

• Electrical Characteristics

Watts	50 W
-------	------

Lamp Wattage	50.0 W
Lamp Voltage	150 V
Lamp Current	0.430 A
Dimmable	Yes

• Product Dimensions


Base Face to Base Face A	539.2 (max) mm
Insertion Length B	565 (max) mm
Overall Length C	571.6 (max) mm
Diameter D	39.0 (max) mm
Diameter D1	18.0 (max) mm

• Product Data

Product number	347708
Full product name	Error EOC
Short product name	Error EOC
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677347703
Bar code on case	50046677347708
Logistics code(s)	927908508427
tpd_ilcos_cd	FSD-50/40/1B-L/P-2G11
eop_net_weight_pp	140.000 gr


Dimensional drawing

Dimensional drawing



2G11, 4P

Product	A (Max)	B (Max)	C (Max)	D (Max)	D1 (Max)
PL-L 50W/841/4P RS	539.2	565	571.6	39.0	18.0



2G11



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change