



PL-L Energy Advantage

PL-L XEW IS 40W/830/4P/25W 1CT

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

• General Characteristics

Base	2G11
Base Information	4P

Lamp Wattage EL	29.0 W
Lamp Voltage EL	127 V
Lamp Current EL	0.285 A

• Light Technical Characteristics

Color Code	830 [CCT of 3000K]
Color Rendering Index	82 Ra8
Color Designation	Warm White
Color Temperature	3000 K
Chromaticity Coordinate X	440 -
Chromaticity Coordinate Y	403 -
Initial Lumens	2600 Lm
Lumen Maintenance EL 2000h	90 %
Lumen Maintenance EL 5000h	85 %
Lumen Maintenance EL 15000h	90 %

• Product Dimensions

Base Face to Base Face A	539.2 (max) mm
Insertion Length B	565.0 (max) mm
Overall Length C	571.6 (max) mm
Diameter D	39.0 (max) mm
Diameter D1	18.0 (max) mm

• Product Data


Product number	209130
Full product name	PL-L XEW IS 40W/830/4P/25W 1CT
Short product name	PL-L 40W/830/XEW/4P/IS 25W
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677209131
Bar code on case	50046677209136
Logistics code(s)	927908383021
eop_net_weight_pp	140.000 gr

• Electrical Characteristics

Watts	40 W
-------	------


Dimensional drawing

Dimensional drawing




2G11, 4P

Product	A (Max)	B (Max)	C (Max)	D (Max)	D1 (Max)
PL-L 40W/830/4P	539.2	565.0	571.6	39.0	18.0



2G11

Photometric data



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change