



Ceramalux ALTO

Ceramalux 100W Mog ED23 1/2 CL ALTO

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

• General Characteristics

Base	Mogul [Mogul]
Base Information	Brass [Brass Base]
Bulb	ED23 1/2
Bulb Material	Hard Glass
Bulb Finish	Clear
Operating Position	Universal [Any or Universal (U)]
Main Application	General and Street Lighting
Rated Avg. Life	24000 hr

• Light Technical Characteristics

Color Rendering Index	21 Ra8
Color Temperature	2100 K
Color Temperature technical	2100 K
Initial Lumens	10000 Lm
Luminous Efficacy Lamp	100 Lm/W
Design Mean Lumens	8460 Lm
Chromaticity Coordinate X	520 -
Chromaticity Coordinate Y	420 -

• Electrical Characteristics

Watts	100 W
Lamp Voltage	55 V
Lamp Current	2.1 A
Ignition Time	5 (max) s
Re-ignition Time [min]	2 (max) min

• Environmental Characteristics

Mercury (Hg) Content	22.1 (max) mg
----------------------	---------------

• UV-related Characteristics

• Luminaire Design Requirements

Cap-Base Temperature	210 (max) C
Bulb Temperature	400 (max) C

• Product Dimensions



Light Center Length L	5 in
Max Overall Length (MOL) - C	7.75 (max) in
Diameter D	2.125 in

• Product Data

Product number	368720
Full product name	Ceramalux 100W Mog ED23 1/2 CL ALTO
Short product name	Ceramalux 100W Mog ED23 1/2 CL ALTO
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677368722
Bar code on case	50046677368727
Logistics code(s)	928601139801
eop_net_weight_pp	0.123 kg

PHILIPS

Dimensional drawing



E39

Ceramalux 100W Mog ED23 1/2 CL ALTO



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, October 31
data subject to change