

XJG Type Conduit Expansion Joints

Catalog Number: PRXJG64SA
UPC: 784011219612



Description

2 Inch XJG Aluminum Expansion Joint (4 Inch Movement)

PVC coated XJG type expansion joints are used to connect two lengths of conduit subject to longitudinal movement, including that caused in long runs by thermal expansion and contraction.

Application

- Used to connect two lengths of conduit subject to longitudinal movement, including thermal expansion and contraction

Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- 10 trade sizes from 1/2" through 4"
- Sealing sleeves on all conduit openings
- Available with either 4" or 8" maximum movement
- Internally Grounded

General

Material:	ALUMINUM
Exterior Finish:	A nominal .040 inch (40 mil) gray PVC coating
Interior Finish:	A nominal .002 inch (2 mil) red urethane
Grounding:	Internal
Longitudinal Movement:	4 Inch

Dimensions

Dimension A (Inches):	4.83
Dimension B (Inches):	8.25

Standards

NEC:	Article 250-77
NEC:	Article 300-7 (b)
NEMA:	FB1

