

XJG Type Conduit Expansion Joints

Catalog Number: PRXJG104
UPC: 784011208388

Description

4 Inch XJG Expansion Joint (4 Inch Movement)

PVC coated XJG type expansion joints are used to connect two lengths of conduit subject to longitudinal movement, including that caused in long runs by thermal expansion and contraction.

Application

- Used to connect two lengths of conduit subject to longitudinal movement, including thermal expansion and contraction
- Used to connect two lengths of conduit subject to longitudinal movement, including thermal expansion and contraction

Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- 10 trade sizes from 1/2" through 4"
- Sealing sleeves on all conduit openings
- Available with either 4" or 8" maximum movement
- Internally Grounded

General


Material:	FERROUS METAL
Exterior Finish:	A nominal .040 inch (40 mil) gray PVC coating
Interior Finish:	A nominal .002 inch (2 mil) red urethane
Grounding:	Internal
Longitudinal Movement:	4 Inch

Dimensions

Dimension A (Inches)	6.7
Dimension B (Inches)	9.81
Nominal Weight (Pounds)	22.5

Technical / Specification Documents

Specification Guide (1995 Master)	AVAILABLE ON WEBSITE
Specification Guide (2004 Master)	AVAILABLE ON WEBSITE
Installer Certification and Tools	AVAILABLE ON WEBSITE
Chemical Resistance Charts	AVAILABLE ON WEBSITE
Performance Specifications	AVAILABLE ON WEBSITE





XJG Type Conduit Expansion Joints

Catalog Number: PRXJG104
UPC: 784011208388

Standards

NEC:	Article 250-77
NEC:	Article 300-7 (b)
NEMA:	FB1