

AURORA

AURORA LOGGER

RESIDENTIAL

GENERAL SPECIFICATIONS

The Aurora Logger Residential is a high-performance, customer data management system for home PV system operations. This system manager collects data from Power-one inverters, logs it on site, and then acts as an internet gateway to send the data to be stored on Power-One's servers where it is accessible via a web browser.

The residential solution allows home owners to track energy production that will both; demonstrate the environmental benefits such as carbon reduction; and will make performance degradation more visible indicating the need for timely cleaning or maintenance.


Aurora Logger Residential model includes:

- Data management system with serial and Ethernet ports to provide data logging for 5 Power-One inverters
- 12 VDC, 1A power supply



Features

- Quick installation and fast provisioning (Including DHCP client for Auto IP assignment)
- Collects data and uploads information over the Internet in near real-time to the Aurora Vision platform
- Reliable, secure transmission of operational data to Aurora Vision. Time-stamps and CRC checksums are used to secure data log files and prevent tampering
- Remote configuration capabilities facilitate upgrades over the Internet



Block Diagram

TECHNICAL DATA	AURORA LOGGER RESIDENTIAL
	VSN-MGR-RES-P1
Platform	
Computing Environment	High performance embedded computing platform
Performance Management	Compatible with Aurora Vision and Aurora Easy View software-as-a-Service solutions for real time performance management and reporting
Monitoring	Inverter Direct
Communication Interfaces	
Serial Port Interface	(2) RS-485 + (2) RS-232
RS-485 Port Configuration	Non-isolated Modbus or Power-One protocol support
RS-232 Port Configuration	Modbus
Maximum Devices	5 Power-One Inverters
Fieldbus Cable	RS-485 Shielded twisted pair. Recommend Belden #3016A for 3 conductors
Ethernet Port 0	Firewall protected Ethernet WAN port for internet connection
Ethernet Port 1	Local LAN with static IP address
Ethernet Connections	RJ-45 Ethernet 10/100 base-T (LAN/WAN)
Communication Protocol	
Plant Fieldbus Protocols	Power-One, Modbus RTU, SunSpec
LAN/WAN Protocols	Modbus/TCP, HTTP, DHCP, SSL, SSH, FTP, XML
Data Logging Specifications	
Data Sampling Rate	High frequency data sampling - 1 minute average
Logging	Real time power values at 15-minute intervals. Other intervals available.
Local Storage	Log data for 30 days based on 15-minute intervals. (Days logged reduced by intervals shorter than 15-minute)
Upgradeability	Field upgradable over the Internet or locally via USB memory stick
Power Supply	
DC Power Supply Input	100 - 240 VAC
DC Power Supply Output	12VDC, 1A
Environmental Protection Rating	
Ambient Temperature Range	0°C to 40°C
Environmental Protection Rating	IP20
Compliance	
Humidity	0 to 90% non condensing
Emission	FCC Part 15 Class B, CISPR 22, EN 55022 Conducted and Radiated Emission
Immunity	EN55024
Physical Parameters (per unit)	
Dimensions	5.5" x 5.25" x 1" (.14m .13m x .03m)
Weight	2 lbs (0.91 kg)



www.power-one.com

Power-One Kenewabie Energy	worldwide Sales Offices
	AI /D

Country	Name/Region	<u>Telephone</u>	<u>Email</u>
Australia	Asia Pacific	+61 2 9735 3111	sales.australia@power-one.com
China (Shenzhen)	Asia Pacific	+86 755 2988 5888	sales.china@power-one.com
China (Shanghai)	Asia Pacific	+86 21 5505 6907	sales.china@power-one.com
India	Asia Pacific	+65 6896 3363	sales.india@power-one.com
Singapore	Asia Pacific	+65 6896 3363	sales.singapore@power-one.com
Belgium / The Netherlands / Luxembourg	Europe	+32 2 206 0338	sales.belgium@power-one.com
France	Europe	+33 (0) 141 796 140	sales.france@power-one.com
Germany	Europe	+49 7641 955 2020	sales.germany@power-one.com
Italy	Europe	00 800 00287672 Opt. n°5	sales.italy@power-one.com
Spain	Europe	+34 91 879 88 54	sales.spain@power-one.com
United Kingdom	Europe	+44 1903 823 323	sales.UK@power-one.com
Dubai	Middle East	+971 50 100 4142	sales.dubai@power-one.com
Canada	North America	+1 877 261-1374	sales.canada@power-one.com
USA East	North America	+1 877 261-1374	sales.usaeast@power-one.com
USA Central	North America	+1 877 261-1374	sales.usacentral@power-one.com
USA West	North America	+1 877 261-1374	sales.usawest@power-one.com