

OE Series Conduit Outlet Boxes

Catalog Number: PROELB2
UPC: 784011206445

Description

3/4 Inch OELB Outlet Box w/ Cover (Elbow Body, 2 Conduit Openings)

PVC coated OE Series Conduit Outlet Boxes are installed in hazardous location conduit systems to serve as pulling and splicing fittings, to connect runs of conduit, to change the direction of a conduit run, or to provide access to conductors.

Application

- Installed in hazardous location to serve as pull and splice boxes, to change the direction of a conduit run, to connect runs of conduit, or to provide access to conductors

Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- Available in 1/2" or 3/4" trade sizes
- Molded in PVC cover to body gasket seals corrosives out
- Sealing sleeves on all conduit openings
- Compact design saves space
- Encapsulated stainless steel cover screws

General

Material:	FERROUS METAL
Exterior Finish:	A nominal .040 inch (40 mil) Gray PVC Coating
Interior Finish:	A nominal .002 inch (2 mil) red urethane
Seal Type:	Molded in PVC cover and body gasket
Body Design:	Compact Design
Hazardous Location:	Designed for hazardous location application
Conduit Opening:	Two, positioned in 90 degree angle

Dimensions

Dimension A (Inches)	4.39
Dimension B (Inches)	1.96
Dimension C (Inches)	2.14
Dimension D (Inches)	0.69
Nominal Weight (Pounds)	3





OE Series Conduit Outlet Boxes

Catalog Number: PROELB2
UPC: 784011206445

Technical / Specification Documents

Specification Guide (1995 Master) *AVAILABLE ON WEBSITE*

Specification Guide (2004 Master) *AVAILABLE ON WEBSITE*

Installer Certification and Tools *AVAILABLE ON WEBSITE*

Chemical Resistance Charts *AVAILABLE ON WEBSITE*

Performance Specifications *AVAILABLE ON WEBSITE*

Standards

NEC/CEC: Class I, Division 1 & 2, Groups C, D

NEC/CEC: Class II, Division 1, Groups E, F, G

NEC/CEC: Class II, Division 2, Groups F, G

NEC/CEC: Class III

