



22-6 Shielded Plenum

ETL listed for guaranteed performance
Made in the USA

Part No.: 725228S

Applications:

This document establishes the specifications for a plenum rated six conductor shielded cable used for communication applications.

Construction Details:

Number of Conductors: 6/C
Conductor: 22AWG Stranded Bare Copper
Insulation Material: Remguard Plenum Polymer
Nominal Insulation Thickness: 0.007 in.
Nominal Insulation Diameter: 0.043 in.
Color Code: Black, Blue, Green,
Brown, Natural, Red
Shield: Aluminum/Polyester Tape (100% Coverage)
Drain: Stranded Tin Copper
Jacket Material: Remguard Plenum Polymer
Nominal Jacket thickness: 0.015 in.
Nominal Diameter: 0.165 in.
Surface Print: 3122598 CMP 22AWG C(ETL)US
FT6 + Sequential Footage Marking

Electricals:

Suggested Working Voltage: 300 Volts, rms.

Technical Details:

Temperature Rating

Operation: -2°C to +60°C

Nominal Weight: 22 lbs. / 1,000 feet

Standards:

- NEC Article 800
- UL Subject 444, Type CMP

Codes & Listings:

- C(ETL)US

Preparation for Shipment:

The cable shall be packaged to preclude the inducement of damage due to handling and transportation, and shall be in accordance with the best commercial practices available. Shipping containers shall be constructed as to eliminate any possible damage to the cables due to shipment.



MADE IN THE USA



Issue Date: 07/12
Revision: 0

All warranty information can be viewed at WWW.REMEE.COM.

This product is RoHS compliant to directive 2002/95/EC .

1751 State RTE. 17A STE #1 Florida, NY 10921
Customer Service: 800-431-3864 Fax: 845-651-4160 Website: www.remee.com

It is the sole responsibility of the user to have the most current specification. Specifications are subject to change without notice.