

LA Circuit Breakers

Table 9.131: L-frame—400 A, Thermal-magnetic (600 Vac)



FI36100
2- and 3-pole
4.5 in (114 mm)
Mounting Height

Ampere Rating	AC Magnetic Trip Settings		Standard Interrupting	Terminal Wire Range
	Low	High	Catalog Number	
2-pole, 600 Vac, 250 Vdc [24]				
125 A	625	1250	LA26125()	AL400LA one #1 AWG–600 kcmil or two #1 AWG–250 kcmil AL or Cu
150 A	750	1500	LA26150()	
175 A	875	1750	LA26175()	
200 A	1000	2000	LA26200()	
225 A	1125	2250	LA26225()	
250 A	1250	2500	LA26250()	
300 A	1500	3000	LA26300()	
350 A	1750	3500	LA26350()	
400 A	2000	4000	LA26400()	
3-pole, 600 Vac, 250 Vdc				
125 A	625	1250	LA36125	AL400LA one #1 AWG–600 kcmil or two #1 AWG–250 kcmil AL or Cu
150 A	750	1500	LA36150	
175 A	875	1750	LA36175	
200 A	1000	2000	LA36200	
225 A	1125	2250	LA36225	
250 A	1250	2500	LA36250	
300 A	1500	3000	LA36300	
350 A	1750	3500	LA36350	
400 A	2000	4000	LA36400	

L-frame accessories starting on Supplemental Digest Section 3.

L-frame dimensions [Molded Case Circuit Breaker Dimensions, page 7-74.](#)

L-frame optional lugs [Mechanical Lugs, page 7-58.](#)

Table 9.132: Interrupt Ratings (kA)

	LA	LC	LI
240 V	42	100	200
480 V	30	65	200
600 V	22	35	100

[24] 2-pole circuit breaker catalog numbers are completed by adding required phase connection letters as suffix to catalog number. See [page 9-39.](#)