

Product data sheet

Characteristics

9007C62ED

9007C limit switch - 2 NO/NC - top push rod plunger - adjustable

Product availability: Stock - Normally stocked in distribution facility

Price*: 236.00 USD



Main

Commercial Status	Commercialised
Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch
Product specific application	Standard box
Device short name	9007C
Body type	Plug-in
Head type	Plunger head
Material	Metal
Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Stainless steel spring return plunger (adjustable)
Switch actuation	On end
Type of approach	1 direction vertical approach
Electrical connection	(12...22 AWG) screw-clamp terminals, 1...2
Cable entry	1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1
Number of poles	2
Contacts type and composition	2(NC-NO)
Contacts operation	Snap action
Positive opening	Without
Sale per indivisible quantity	1

Complementary

Body material	Zinc
Head material	Zinc
Function available	-
Switch function	DPDT-DB
Contact form	Form ZZ
Contacts material	Silver contacts
Terminals description ISO n°1	(1-2)NC (3-4)NO (5-6)NC (7-8)NO
Repeat accuracy	+/- 0.001 in linear travel of cam
[Ie] rated operational current	0.55 A at 125 V DC, R300 conforming to NEMA 0.11 A at 250 V DC, R300 conforming to NEMA 6 A at 120 V AC, A600 conforming to NEMA 3 A at 240 V AC, A600 conforming to NEMA 1.5 A at 480 V AC, A600 conforming to NEMA 1.2 A at 600 V AC, A600 conforming to NEMA
[Ithe] conventional enclosed thermal current	10 A

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

[Ui] rated insulation voltage	600 V degree of pollution 3 conforming to CSA C22.2 No 14 for contact block 600 V degree of pollution 3 conforming to UL 508 for contact block
[Uimp] rated impulse withstand voltage	2.64 kV AC for 1 s conforming to CSA 2.2 kV AC for 1 min conforming to UL 2.5 kV AC for 1 min conforming to CE
Short circuit protection	10 A by CC fuse, protection type: non-time delay
Electrical durability	1000000 cycles
Local signalling	Without
Mechanical durability	10000000 cycles
Width	1.55 in
Height	5.22 in
Depth	1.79 in
Product weight	1.25 lb(US)


Environment

Shock resistance	60 gn (duration = 9 ms) conforming to IEC 60068-2-27
Vibration resistance	25 gn (f = 10...150 Hz) conforming to IEC 60068-2-6
NEMA degree of protection	NEMA 13 conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 2 conforming to Nema type 250 NEMA 1 conforming to Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Class of protection against electric shock	Class 0 conforming to IEC 61140
Ambient air temperature for operation	-20...185 °F for standard environment
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment
Protective treatment	Epoxy powder coat

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901540564
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
Product environmental profile	Available  Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------