



# 9001K34J35LGFG

illuminated selector switch Ø30 - green- 2 position spring return right to left



[Download your 9001K34J35LGFG datasheet](#)

[Characteristics](#) | [Documents & Downloads](#)

[Change your selection](#)

[Discover other products & accessories](#)



[Discover your Schneider Electric tools](#)

## Main Hide

|                                  |                                      |
|----------------------------------|--------------------------------------|
| <b>Range of product</b>          | Harmony 9001K                        |
| <b>Product or component type</b> | Complete illuminated selector switch |
| <b>Device short name</b>         | 9001K                                |
| <b>Type of operator</b>          | Spring return (right to left)        |
| <b>Operator profile</b>          | Long handle                          |

## Complementary Hide

|                                      |                                  |
|--------------------------------------|----------------------------------|
| <b>Bezel material</b>                | Chromium plated metal            |
| <b>Mounting diameter</b>             | 30 mm                            |
| <b>Product weight</b>                | 0.245 kg                         |
| <b>Shape of signaling unit head</b>  | Octagonal                        |
| <b>Operator position information</b> | 2 positions                      |
| <b>Contacts type and composition</b> | Without contact block            |
| <b>Mechanical durability</b>         | 500000 cycles                    |
| <b>Light source</b>                  | High luminosity LED              |
| <b>Light source</b>                  | High luminosity LED              |
| <b>Bulb base</b>                     | BA 9s                            |
| <b>Light block colour</b>            | Green                            |
| <b>[Us] rated supply voltage</b>     | 24 V AC/DC                       |
| <b>[Us] rated supply voltage</b>     | 24 V AC/DC                       |
| <b>Product compatibility</b>         | 9001KA2, mounting on side 1 or 2 |

## Environment Hide

|   |  |
|---|--|
| <b>Protective treatment</b>                       | TC   |
| <b>Ambient air temperature for storage</b>        | -40...70 °C                                      |
| <b>Ambient air temperature for operation</b>      | -25...70 °C                                      |
| <b>Class of protection against electric shock</b> | Class II conforming to IEC 61140                 |
| <b>IP degree of protection</b>                    | IP66 conforming to IEC 60529                     |
| <b>NEMA degree of protection</b>                  | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3 |

|                               |  |
|-------------------------------|--|
|                               | NEMA 3R<br>NEMA 4  |
| <b>Standards</b>              | EN/IEC 60947-1<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>JIS C 4520<br>JIS C 852<br>UL 508<br>CSA C22.2 No 14 |
| <b>Product certifications</b> | NEMA<br>UL 508   |
| <b>Vibration resistance</b>   | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6  |
| <b>Shock resistance</b>       | 50 gn conforming to IEC 60068-2-27   |

### Offer Sustainability

 [Hide](#)

|                               |   |
|-------------------------------|---|
| <b>RoHS (date code: YYWW)</b> | Compliant - since 0921 - Schneider Electric declaration of conformity |
| <b>REACH</b>                  | Reference not containing SVHC above the threshold                     |