



### Main

Range of product	Harmony XB5R
Product or component type	Empty control station
Device short name	XB5R
Product destination	For XB5R Ø 22 mm control units
Control station application	One function

### Complementary

Colour of base of enclosure	Dark grey RAL 7016
Material	Polycarbonate
CAD overall width	100.6 mm
CAD overall height	60 mm
Product weight	0.2 kg


### Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...55 °C
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK03 conforming to EN 50102
Standards	CSA C22-2 No 14 EN/IEC 60947-5-1 UL 508 EN 300-440-1 EN 300-440-2 EN 301-489-1 EN 301-489-3
Product certifications	CE C-Tick FCC GOST ANATEL SRRC BT 2006/95/EC EMC directive 2004/108/EC R&TTE directive 1999/5/EC RSS

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Wireless and Batteryless Pushbutton - Transmitter

Plastic Handy Box for Mobile Use



- (1) Location for ZBY0101T legend.
- (2) Location for magnet to be stuck on by the customer.