

5SM3311-6KK13



RES.CURRENT OP.CIRCUIT BREAKER TYPE A 16A 1+N-POL IFN 30MA 24-125V 2M

Notes

For this product a successor is available: 5SV3311-6KK13

List Price	Show prices
Customer Price	Show prices
DataSheet in PDF	Download
Service & Support (Manuals, Certificates, FAQs...)	Download

Product

Article Number (Market Facing Number)	5SM3311-6KK13
Product Description	RES.CURRENT OP.CIRCUIT BREAKER TYPE A 16A 1+N-POL IFN 30MA 24-125V 2M
Product family	RCCBs
Product Lifecycle (PLM)	PM400:Phase Out Started
PLM Effective Date	Product phase-out since: 31.12.2015
Notes	For this product a successor is available: 5SV3311-6KK13

Successor information

Successor	5SV3311-6KK13
Successor Description	Not available

Price data

Price Group	11C
List Price	Show prices
Customer Price	Show prices
Surcharge for Raw Materials	None
Metal Factor	L-O----

Delivery information

Export Control Regulations	AL : N / ECCN : N
Standard lead time ex-works	30 Day/Days
Net Weight (kg)	0,242 Kg
Product Dimensions (W x L x H)	Not available
Packaging Dimension	21,00 x 95,00 x 83,00
Package size unit of measure	MM
Quantity Unit	1 Piece
Packaging Quantity	1

Additional Product Information

EAN	4001869325958
UPC	Not available
Commodity Code	85362010
LKZ_FDB/ CatalogID	LV10.1
Product Group	5511
Country of origin	Germany
Compliance with the substance restrictions according to RoHS directive	Since: 01.06.2006
Product class	B: return restricted, please contact your Siemens partner/contact
Obligation Category for taking back electrical and electronic equipment after use	No obligation to take back electrical and electronic equipment after use

Classifications

	Version	Classification
eClass	5.1	27-14-22-01
eClass	6	27-14-22-01
eClass	7.1	27-14-22-01
eClass	8	27-14-22-01
eClass	9	27-14-22-01
eClass	9.1	27-14-22-01
ETIM	4	EC000003
ETIM	5	EC000003
ETIM	6	EC000003
IDEA	4	4875
UNSPSC	14	39-12-16-26
UNSPSC	15	39-12-16-01