



SUNNY BOY 5000-US / 6000-US / 7000-US / 8000-US

SB 5000US / SB 6000US / SB 7000US / SB 8000US



ASSEMBLED IN THE USA



UL Certified

- For countries that require UL certification (UL 1741/IEEE 1547)

Efficient

- 97% peak efficiency
- OptiCool™ active temperature management system

Safe

- Galvanic isolation

Simple

- Patented automatic grid voltage detection*
- Integrated DC disconnect switch

SUNNY BOY 5000-US / 6000-US / 7000-US / 8000-US


Versatile performer with UL Certification

The Sunny Boy 5000-US, 6000-US, 7000-US and 8000-US inverters are UL Certified and feature excellent efficiency. Graduated power classes provide flexibility in system design. Automatic grid voltage detection* and an integrated DC disconnect switch simplify installation, ensuring safety as well as saving time. These models feature galvanic isolation and can be used with all types of modules—crystalline as well as thin-film.


* US Patent US7352549B1

Technical data	Sunny Boy 5000-US			Sunny Boy 6000-US			Sunny Boy 7000-US			Sunny Boy 8000-US	
	208 V AC	240 V AC	277 V AC	208 V AC	240 V AC	277 V AC	208 V AC	240 V AC	277 V AC	240 V AC	277 V AC
Input (DC)											
Max. recommended PV power (@ module STC)	6250 W			7500 W			8750 W			10000 W	
Max. DC power (@ $\cos \phi = 1$)	5300 W			6350 W			7400 W			8600 W	
Max. DC voltage	600 V			600 V			600 V			600 V	
DC nominal voltage	310 V			310 V			310 V			345 V	
MPP voltage range	250 V - 480 V			250 V - 480 V			250 V - 480 V			300 V - 480 V	
Min. DC voltage / start voltage	250 V / 300 V			250 V / 300 V			250 V / 300 V			300 V / 365 V	
Max. input current / per string (at DC disconnect)	21 A / 20 A 36 A @ combined terminal			25 A / 20 A 36 A @ combined terminal			30 A / 20 A 36 A @ combined terminal			30 A / 20 A 36 A @ combined terminal	
Number of MPP trackers / fused strings per MPP tracker	1 / 4 (DC disconnect)										
Output (AC)											
AC nominal power	5000 W			6000 W			7000 W			7680 W 8000 W	
Max. AC apparent power	5000 VA			6000 VA			7000 VA			8000 VA	
Nominal AC voltage / adjustable	208 V / ●	240 V / ●	277 V / ●	208 V / ●	240 V / ●	277 V / ●	208 V / ●	240 V / ●	277 V / ●	240 V / ●	277 V / ●
AC voltage range	183 - 229 V	211 - 264 V	244 - 305 V	183 - 229 V	211 - 264 V	244 - 305 V	183 - 229 V	211 - 264 V	244 - 305 V	211 - 264 V	244 - 305 V
AC grid frequency; range	60 Hz; 59.3 - 60.5 Hz			60 Hz; 59.3 - 60.5 Hz			60 Hz; 59.3 - 60.5 Hz			60 Hz; 59.3 - 60.5 Hz	
Max. output current	24 A	21 A	18 A	29 A	25 A	22 A	34 A	29 A	25 A	32 A	29 A
Power factor ($\cos \phi$)	1			1			1			1	
Phase conductors / connection phases	1/2	1/2	1/1	1/2	1/2	1/1	1/2	1/2	1/1	1/2	1/1
Harmonics	< 4%			< 4%			< 4%			< 4%	
Efficiency											
Max. efficiency	96.7%	96.8%	96.8%	96.9%	96.8%	97.0%	97.1%	96.9%	97.0%	96.3%	96.5%
CEC efficiency	95.5%	95.5%	95.5%	95.5%	95.5%	96.0%	95.5%	96.0%	96.0%	96.0%	96.0%
Protection devices											
DC reverse-polarity protection	●			●			●			●	
AC short circuit protection	●			●			●			●	
Galvanically isolated / all-pole sensitive monitoring unit	●/-			●/-			●/-			●/-	
Protection class / overvoltage category	I / III			I / III			I / III			I / III	
General data											
Dimensions (W / H / D) in mm (in)	470 / 615 / 240 (18.5 / 24 / 9)										
DC Disconnect dimensions (W / H / D) in mm (in)	187 / 297 / 190 (7 / 12 / 7.5)										
Packing dimensions (W / H / D) in mm (in)	390 / 580 / 800 (16 / 23 / 31.5)										
DC Disconnect packing dimensions (W / H / D) in mm (in)	370 / 240 / 280 (15 / 9 / 11)										
Weight / DC Disconnect weight	64 kg (141 lb) / 3.5 kg (8 lb)									66 kg (145 lb) / 3.5 kg (8 lb)	
Packing weight / DC Disconnect packing weight	67 kg (147 lb) / 4 kg (9 lb)									69 kg (152 lb) / 4 kg (9 lb)	
Operating temperature range (full power)**	-25 °C ... +45 °C (-13 °F ... +113 °F)										
Noise emission (typical)	44 dB(A)			45 dB(A)			46 dB(A)			49 dB(A)	
Internal consumption at night	0.1 W			0.1 W			0.1 W			0.1 W	
Topology	LF transformer			LF transformer			LF transformer			LF transformer	
Cooling concept	OptiCool			OptiCool			OptiCool			OptiCool	
Electronics protection rating / connection area	NEMA 3R / NEMA 3R			NEMA 3R / NEMA 3R			NEMA 3R / NEMA 3R			NEMA 3R / NEMA 3R	
Features											
Display: text line / graphic	●/-			●/-			●/-			●/-	
Interfaces: RS485 / Bluetooth®	○/○			○/○			○/○			○/○	
Warranty: 10 / 15 / 20 years	●/○/○			●/○/○			●/○/○			●/○/○	
Certificates and permits (more available on request)	UL1741, UL1998, IEEE 1547, FCC Part 15 (Class A & B), CSA C22.2 No. 107.1-2001										
**Extended operating temperature range to -40 °C available. Specify when ordering.											
NOTE: US inverters ship with gray lids. Data at nominal conditions											
● Standard features ○ Optional features - Not available											
Type designation	SB 5000US			SB 6000US			SB 7000US			SB 8000US	


SUNNYBOY5078/DUS120731 Sunny Boy, OptiCool and SMA are registered trademarks of SMA Solar Technology AG. Text and figures comply with the state of the art applicable when printing. Subject to technical changes. We accept no liability for typographical and other errors. Printed on chlorine-free paper.




Accessories




RS485 interface
485USPB-SMC-NR



Bluetooth Piggy Back
BTPBINV-NR



Combi-Switch
DC disconnect and PV
array combiner box
COMBO-SWITCH



Combiner Box
Simplify wiring for added
convenience and safety
SBCB-6-3R or SBCB-6-4