



LED Lamps with Smooth Warm Dimming

Introducing TCP's Allusion "incandescent-like" LED smooth warm dimming technology. LEDs with a unique dimming profile that replicates true incandescent/halogen dimming.

Limitless options for the following applications:

- Table Lamps
- Floor Lamps
- Sconces
- Ceiling Fixtures
- Decorative Lighting
- Chandeliers
- Recessed Downlights
- Track Lights
- Dimmable 6" & 5" Downlight applications

Great features and benefits:

- Energy efficient: Up to 85% more efficient than incandescent/halogen replacements
- Long life: 25,000 hours
- Dimming Range (CCT):

A19 – 2700K to 2000K	PAR30 – 3000K to 2000K
B11 – 2400K to 1900K	PAR38 – 3000K to 2000K
BR30 – 3000K to 2000K	5"/6" Downlight – 3000K to 2000K
- Similar look and feel as incandescent alternative
- Approved for damp locations



Allusion™

we know light.™





with Smooth Warm Dimming


LED 25,000 hours average rated life, 120 volts

Applications:

Perfect for hospitality applications that rely on mood setting.

- + Table Lamps
- + Floor Lamps
- + Sconces
- + Ceiling Fixtures
- + Decorative Lighting
- + Chandeliers
- + Recessed Downlights
- + Track Lights
- + Dimmable 6" & 5" Downlight applications

Features	Benefits
Up to 85% less energy than incandescent/halogen replacements	Instant energy savings
Smooth warm dimming	Creates the perfect atmosphere
Long life	Minimizes replacement and maintenance costs
Shatter resistant	Lower the risk of injury and breakage
UL approved for damp locations	Can be used outdoors in enclosed fixtures



Specifications

Input Line Voltage: 120 VAC
 Input Power See Chart
 Input Line Frequency 50/60HZ
 Lamp Life (Rated) 25,000 hrs
 Minimum Starting Temp -30°C
 Maximum Operating Temp..... 40°C
 CRI 80

Allusion™



Warranties and Certifications:	Item #	Description	Voltage	Wattage	Incandescent/Halogen Wattage Comparison	Lumens	LPW	CCT	CRI	R9	M.O.L. (inches)	Diameter (inches)	
5 YEAR WARRANTY 	TCP Allusion LED Lamps – with SMOOTH WARM DIMMING												
	LED9A19DA	9W A19 A-Lamp	120	9	60	650	72.2	2700K to 2000K	80	>0	4.6	2.4	
	LED5E12B11DA	5W B11 Candelabra Blunt Tip	120	5	25	300	60.0	2400K to 1900K	80	>0	3.8	1.4	
	LED10BR30DA	10W BR30	120	10	65	675	67.5	3000K to 2000K	80	>0	5.4	3.8	
	LED15P30DA	15W PAR30—25° Beam Angle	120	15	100	950	63.3	3000K to 2000K	80	>0	4.6	3.8	
	LED15P38DA	15W PAR38—25° Beam Angle	120	15	100	975	65.0	3000K to 2000K	80	>0	5.2	4.8	
	LED10DR56DA	10W 5"/6" Recessed Downlight	120	10	65	700	70.0	3000K to 2000K	80	>0	2.3	7.5	

*Based on 12 hours use per day For the most up-to-date specs, please visit www.tcp.com

