

ES Series Single Phase Main Lug & Main Breaker Load Centers

1-phase, 3-wire SN, 120/240 Volts AC

Main Breaker/Convertible Load Centers^①

12-70 Circuits / 100-225 Amperes

Aluminum Bus

60/75°C Rated 22,000A IR^②

Branch Circuits			Indoor Enclosure – NEMA Type 1		Outdoor Enclosure – NEMA Type 3R	
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number	Enclosure Height (inches) ^③	Catalog Number	Enclosure Height (inches) ^②
100	10	20	S1020B1100 NEW!	18	—	—
100	12	24	S1224B1100	18	SW1224B1100	21
100	16	24	S1624B1100	21	SW1624B1100	23
100	20	20	S2020B1100	24	SW2020B1100	27
100	20	24	S2024B1100	24	—	—
100	30	30	S3030B1100	30	—	—
125	12	24	—	—	SW1224B1125 NEW!	21
125	16	24	S1624B1125 NEW!	21	—	—
125	16	32	—	—	SW2024B1125 NEW!	27
125	24	24	S2424B1125	24	SW2424B1125 NEW!	27
125	30	30	S3030B1125	30	—	—
125	30	40	S3040B1125 NEW!	30	SW3040B1125 NEW!	35
150	16	30	S1630B1150	24	—	—
150	20	30	S2030B1150	24	—	—
150	24	30	S2430B1150	30	—	—
150	30	30	S3030B1150	30	—	—
150	30	40	S3040B1150 NEW!	30	SW3040B1150 NEW!	35
150	40	40	—	—	SW4040B1150 NEW!	38
200	16	32	S1632B1200 NEW!	24	—	—
200	20	40	S2040B1200	30	SW2040B1200	27
200	24	40	S2440B1200	30	—	—
200	30	40	S3040B1200	36	SW3040B1200	35
200	40	40	S4040B1200	36	SW4040B1200	38
200	54	70	S5470B1200 NEW!	44	—	—
225	42	60	S4260B1225	39	SW4260B1225	42
225	54	70	S5470B1225	44	—	—

Main Lug/Non-convertible Load Centers

12-70 Circuits / 125-225 Amperes

Aluminum Bus

60/75° Rated 100,000A IR

Branch Circuits			Indoor Enclosure - NEMA Type 1		Outdoor Enclosure - NEMA Type 3R	
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number	Enclosure Height (inches) ^③	Catalog Number	Enclosure Height (inches) ^②
125	12	12	S1212L1125 ^⑤	18	SW1212L1125 ^⑤	21
125	12	24	S1224L1125 ^⑤	18	SW1224L1125 ^⑤	21
125	16	24	S1624L1125	21	SW1624L1125	21
125	20	20	S2020L1125	21	—	—
125	20	20	S2020L1125G ^⑥	21	—	—
125	20	24	S2024L1125	21	—	—
125	20	24	S2024L1125G ^⑥	21	—	—
125	24	24	S2424L1125	24	SW2424L1125	27
125	24	24	S2424L1125G ^⑥	24	—	—
125	24	40	S2440L1125	24	—	—
125	30	40	S3040L1125	30	SW3040L1125	29
125	30	40	S3040L1125G ^⑥	30	—	—
125	40	40	S4040L1125	36	—	—
150	20	30	S2030L1150	24	SW2030L1150	27
200	12	24	S1224L1200 ^⑤	21	SW1224L1200 ^⑤	21
200	20	40	S2040L1200	24	SW2040L1200	27
200	24	40	S2440L1200	30	—	—
200	30	30	S3030L1200	30	—	—
200	30	40	S3040L1200	30	SW3040L1200	35
200	30	54	S3054L1200	30	SW3054L1200	35
200	40	40	S4040L1200	36	SW4040L1200	35
225	12	24	—	—	SW1224L1225	23
225	42	60	S4260L1225	36	SW4260L1225	38
225	54	70	S5470L1225	42	—	—

① Suitable for use as service equipment.

② May be installed on higher rated systems when protected by a circuit breaker with a higher AIR rating.

③ Indoor enclosures are 14 1/4" wide by 3 7/8" deep.

④ Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.

⑤ Suitable for use as service entrance equipment when not more than six main disconnecting means are provided. See article 230.71 of the NEC[®].

⑥ ES Series single phase skus with a "G" suffix have ground bar included (factory installed).