


# T&B Liquidtight Fittings



1. COLOR: MACHINE TOOL GRAY
2. MATERIAL: OUTER JACKET PVC  
INNER CORE ALUMINUM
3. WORKING TEMP: -20°C TO 80°C
4. ALL DIMENSIONS ARE NOMINAL  
AND MAY VARY
5. FOR USE WITH STANDARD  
LIQUID TIGHT CONNECTORS

4"	25	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	4.020 (102.1)	4.480 (113.8)	LTA400-25
3"	25	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	3.085 (78.4)	3.480 (88.4)	LTA300-25
2-1/2"	25	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	2.493 (63.3)	2.857 (72.6)	LTA250-25
2"	50	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	2.033 (51.6)	2.358 (59.9)	LTA200-50
1-1/2"	50	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	1.588 (40.3)	1.883 (47.8)	LTA150-50
1-1/4"	50	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	1.395 (35.4)	1.645 (41.8)	LTA125-50
1"	100	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	1.054 (26.8)	1.303 (33.1)	LTA100-100
3/4"	100	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	.830 (21.1)	1.040 (26.4)	LTA75-100
1/2"	100	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	.632 (16.1)	.830 (21.1)	LTA50-100
3/8"	100	ALUMINUM LIQUID TIGHT FLEXIBLE CONDUIT	.494 (12.5)	.700 (17.8)	LTA38-100
SIZE	LENGTH (FT)	DESCRIPTION	INSIDE DIAMETER (IN) (MM)	OUTSIDE DIAMETER (IN)(MM)	CAT #

## GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.

## REVISIONS

- |   |  |
|---|--|
| - | SEE ERN (****) FOR APPROVAL SIGNATURES & RELEASE DATE.<br>PROJECT NO: **** |
|---|--|

**Thomas & Betts**  
www.tnb.com

DESCRIPTION:

**LIQUID TIGHT FLEXIBLE  
CONDUIT ALUMINUM**

ORIGINAL PROJECT NO / ( ERN NO )

**RD55691 / ( 2006750 )**

SHEET NO:

**1 OF 1**

REV. NO:

**-**

DRAWING NO:

**WSD-000277**