

## WEEB Lug

The WEEB Lug consists of a WEEB (Washer, Electrical Equipment Bond), lay-in lug, and hardware. It is used with one solid or stranded copper wire (6AWG to 14AWG), or two copper wires (10AWG to 12AWG) to provide a continuous ground on roof or ground mounted solar systems. Unlike traditional lay-in lugs, the WEEB Lug does not require surface preparation on rail or module to install. The WEEB Lug is installed using a 1/4-20 stainless steel screw which tightens the WEEB, allowing the specialized teeth to embed into anodized aluminum, galvanized steel, or any electrically conductive metal to establish a gas tight electrical connection. The tin-plated Lug assures minimum contact resistance and protection against corrosion. The copper wire is clamped by a 1/4-28 stainless steel screw, which is horizontal to the tang for easy access when mounted under a PV module. The low profile of the WEEB Lug allows it to be installed in a variety of positions and comes with hardware to mount it to a rail or through a 1/4 inch clearance hole.



- Material: 304 stainless steel, tin-plated copper, outdoor rated
- Low profile design
- Multiple equipment ground conductor allowance:  
One 14 AWG to 6 AWG or two 10 AWG, two 12 AWG
- Listed to ANSI/UL 467 by Intertek ETL

