

**GROUP H, K FACTOR 13, 115°C RISE****480 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz**

kVA	CATALOG NO.	APPROX. DIMENSIONS ② Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 15
		HEIGHT	WIDTH	DEPTH				
30.0	TPNS01533121S	29.90 (75.9)	28.20 (71.6)	22.40 (56.9)	400 (181.0)	F ①	WSA2	22-E
45.0	TPNS01533131S	35.90 (91.2)	31.90 (81.0)	26.90 (68.3)	575 (261.0)	F	WSA3	22-E
75.0	TPNS01533141S	35.90 (91.2)	31.90 (81.0)	26.90 (68.3)	750 (340.0)	F	WSA3	22-E
112.5	TPNS01533151S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1120 (508.0)	F	WSA4	22-E
150.0	TPNS01533161S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1200 (544.0)	F	WSA4	22-E

Notes: All TPNS models are TP1 compliant

GROUP M, K FACTOR 13, 150°C RISE**208 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz**

kVA	CATALOG NO.	APPROX. DIMENSIONS ② Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH				
15.0	TPNS01792714S	25.50 (64.8)	24.90 (62.0)	19.37 (49.2)	320 (145.1)	F ①	WSA1	61-E
30.0	TPNS01792724S	25.50 (64.8)	24.90 (62.0)	19.37 (49.2)	366 (166.0)	F ①	WSA1	61-E
45.0	TPNS01792734S	29.40 (74.7)	28.15 (71.5)	22.37 (56.8)	522 (236.8)	F ①	WSA2	61-E
75.0	TPNS01792744S	35.40 (89.9)	31.90 (81.0)	26.87 (68.2)	667 (302.6)	F	WSA3	61-E

Notes: All TPNS models are TP1 compliant

Notes: All TPNS models are TP1 compliant

**For Additional Low Temperature Rise 115° and 80° Degree Units and Copper Wound Units,
Consult Factory****NON-LINEAR LOAD ISOLATION® WIRING DIAGRAMS (Refer to pgs 134-136)****NON-LINEAR LOAD ISOLATION® DESIGN FIGURES (Refer to pg 134)**

① Wall mounting brackets are available for these sizes, refer to page 145.

② Dimensions in this section may change and are not to be used for detailed construction purposes. Please contact the factory for certified dimensional drawings.