



PRODUCTS

SUPPORT

WHERE TO BUY

NEWS & EVENTS

COMPANY

Products > Climbing-Equipment > Extension Ladders > D6300-2 Series > D6324-2 24 ft Type IA Fiberglass D-Rung Extension Ladder



D6324-2 24 ft Type IA Fiberglass D-Rung Extension Ladder

[Write the first review](#)

3 questions | 3 answers [Read all Q&A](#)

Performance Overview

Size	Style	Reach Height	Load Capacity	Type	Performance Rating
24 ft	Multi Section	23 ft	300 lbs	Type IA Duty Rating	

The D6324-2 fiberglass extension ladder has non-conductive rails making this ladder ideal for working near electricity. With a duty rating of 300 pounds, the D6324-2 is durable and long lasting. The exclusive ALFLO® rung joint means TWIST-PROOF® performance on the job. The TRACTION-TRED® D rungs are slip resistant and the side rails are interlocking. The dual action feet are for use on hard or penetrable surfaces and swivel easily. The base and fly sections separate easily to use the base section as a single ladder. The durable rail shield bracket and shoe help protect the bottom of the rail. The fly section rails are pre-pierced at the top for easy field installation of accessories.

Resources

BUY NOW ▶

[View D6300-2 Series Page](#)

[Replacement Parts](#)

[Share](#)

[Email page](#) | [Print this page](#)

Accessories



74-1 Cable Hook



86-1 Spur Shoe



91-2 Adjustable Pole

[+ Show more](#)

Features

- Exclusive ALFLO® rung joint means TWIST-PROOF® performance
- 1-5/8in Slip-resistant TRACTION-TRED® D-rungs
- Smooth operating pulley with polypropylene rope
- Interlocking Side Rails with internal rail guides on bottom of fly section securely connect rails
- External guides at top of base section securely interlock rails
- Heavy Duty extruded rung locks are spring loaded to operate smoothly
- Pre-pierced holes for easy field installation of accessories
- Base and fly separate easily to use base section as single ladder
- Combination Rail Shield Bracket and Shoe with SHU-LOK® and Slip-Resistant Pad
- Molded Rung Braces on bottom step for increased durability
- Mar-Resistant Molded End Caps

Specifications

Feature	Size / Details
Size	24 ft
Reach Height	23 ft
Max Working Length	21 ft
Extended Length	21 ft

Style	Multi Section
Load Capacity	300 lbs
Type	Type IA Duty Rating
Performance Rating	
Material	Fiberglass
Rung Type	D-Rung
Foot Material	Slip-resistant pad
Number of Sections	2
Base Width	19 in outside shoes
Certifications	ANSI A14.5 (2007); OSHA
Approx. Cu. Ft. Per Unit	10.3
Approx. Shipping Wt. Lbs.	52

Dimensions

Feature	Size
Rails Dimension	3-5/16 in
Flange Dimension	1-3/16 in
Rung Dimension	1-5/8 in
Fly Width	16 in

Additional D6300-2 Series Models

Model No.	Size	Reach Height	Max Working Length	Extended Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D6316-2	16 ft	15 ft	13 ft	13 ft	7	36.5
D6320-2	20 ft	19 ft	17 ft	17 ft	8.7	44.5
D6324-2	24 ft	23 ft	21 ft	21 ft	10.3	52
D6328-2	28 ft	27 ft	25 ft	25 ft	12	59.5
D6332-2	32 ft	31 ft	29 ft	29 ft	13.7	71.5
D6336-2	36 ft	34 ft	32 ft	32 ft	15.3	80.5
D6340-2	40 ft	37 ft	35 ft	35 ft	17	88.5

Ratings Summary

Be the first to [write a review](#)

Product Q&A

(3 questions : 3 answers)

Search questions and answers

All

Sort by

PRICE

1 answer

LUCKZ Las Vegas, NV 89108, USA

How to reseal the fiberglass

1 answer

James79761 Dallas, TX, USA asked this on [D6328-2 28' Type IAA Fiberglass D-Rung Extension Ladder](#)

Collapsed length

1 answer

Jim Narberth PA asked this on [D6300-2 Series Fiberglass Multi Section Extension Ladders](#)

1 of 1

PRODUCTS

Climbing Equipment
Fall Protection
Racks & Ramps
Featured Products

SUPPORT

Replacement Parts
Safety Tips
FAQ
Literature
Where to Buy
Login

NEWS & EVENTS

News Releases
Featured Videos
Current Events
Sponsorships
Image Library

COMPANY

Profile
Why Werner
Innovation
Locations
Contact Us
Legal Notices