



Metal Clad Cable Termination Fittings & Accessories

T&B Catalog Number:

ST050-464S

UPC Number:

78621087728

Status:

Active

Description:

Star Teck steel jacketed cable fitting with sealing ring hub size 1/2 inch
Range over jacket 0.600-0.760 inch.

Features

Easy Installation-Exclusive power-grip. Provides a grip that's high up on the cable-not on the first convolution-so strip length and cutting of cable are not critical.

Dependable Service-stainless steel retaining ring. Withstands corrosive environments. Non-magnetic.

Watertight-Tapered bushing. Cone shaped to provide a secure, tight fit while eliminating cupping or water in vertical installations.

Easy to Install In Tight Spaces-Low profile glad nut fits tight spaces. Has grooves for screwdriver installation, and flats for a wrench. Durable and reusable with funnel entry for easy cable insertion.

Application

Provides means for passing armored, metal clad, jacketed cable through a bulkhead or enclosure in hazardous areas. (these fittings are suitable for hazardous areas when used with T&B sealing compound).

Form a mechanical grip and water and/or oil-resistant termination.

Provide grounding continuity of cable armor.

General

Material Steel

Dimension Information

Hub Size (inches)	1/2
Range Over Jacket -Minimum (inches)	.600
Range Over Jacket -Maximum (inches)	.760
Range Over Armor -Minimum (inches)	0.490
Range Over Armor -Maximum (inches)	0.680

Packaging

Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	35.94 lbs. per 100

Application Support

T&B Instruction Sheets	ta00904-tb2
Product Specifications & Overview	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 38947

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com