

## GROUP G



480 DELTA PRIMARY VOLTS — 240 DELTA / 120 TAP SECONDARY VOLTS  
MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz

KVA ②	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 146
		HEIGHT	WIDTH	DEPTH					
3.0	T-2A-53328-1S	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	0.75-1.25 (1.9-3.2)	NA	25-F
6.0	T-2A-53329-1S	11.83 (30.0)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	0.75-1.25 (1.9-3.2)	NA	25-F
9.0	T-2A-53340-1S	14.03 (36.0)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	NA	25-F
15.0	T-3-53341-1S	18.86 (47.9)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	NA	25-I
30.0	T-3-53342-3S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	325 (147.0)	F ①	NA	WS-A-1	26-E
45.0	T-3-53343-3S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	400 (181.0)	F ①	NA	WS-A-1	26-E
75.0	T-3-53344-3S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	500 (226.8)	F ①	NA	WS-A-2	26-E
112.5	T-2A-53345-3S	35.47 (91.2)	31.90 (81.0)	26.88 (68.3)	750 (340.0)	F	NA	WS-A-3	26-E
150.0	T-3-53346-3S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1125 (510.0)	F	NA	WS-A-4	26-E
225.0	T-3-53347-3S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1200 (544.0)	F	NA	WS-A-4	26-E
300.0	T-3-53348-3S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	NA	WS-A-5	26-G
500.0	T-1-53349-3S	62.00 (157.5)	54.00 (137.2)	42.00 (106.7)	2675 (1213.0)	F	NA	WS-B-3	27-G
750.0	T-2-53350-3S	62.80 (159.5)	54.00 (137.2)	41.50 (105.4)	3408 (1545.8)	F	NA	WS-A-6	26-G

NEW

## GROUP GI

480 DELTA PRIMARY VOLTS — SHIELDED UNITS — 240 DELTA / 120 TAP SECONDARY VOLTS  
MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz

KVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 146
		HEIGHT	WIDTH	DEPTH					
30.0	T-79844-3S	29.59 (75.2)	25.15 (63.9)	22.50 (57.2)	365 (165.6)	F	NA	WS-A-8	26-E
45.0	T-79845-3S	29.59 (75.2)	25.15 (63.9)	22.50 (57.2)	460 (208.7)	F	NA	WS-A-8	26-E
75.0	T-79846-3S	29.59 (75.2)	25.15 (63.9)	22.50 (57.2)	530 (240.4)	F	NA	WS-A-8	26-E
*112.5	T-79847-3	35.90 (91.2)	31.90 (81.0)	26.90 (68.3)	630 (285.8)	F	NA	WS-A-3	68-E

\* Non-Shielded Unit

NEW

## GROUP G2

**LOW NOISE (minus 3 db)**

480 DELTA PRIMARY VOLTS — 240 DELTA / 120 TAP SECONDARY VOLTS  
MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz

KVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 146
		HEIGHT	WIDTH	DEPTH					
30.0	LN3-53342-3S	29.48 (74.9)	28.15 (71.5)	22.37 (56.8)	360 (163.3)	F ①	NA	WS-A-2	26-E
45.0	LN3-53343-3S	29.48 (74.9)	28.15 (71.5)	22.37 (56.8)	417 (189.2)	F ①	NA	WS-A-2	26-E
75.0	LN3-53344-3S	35.47 (90.1)	31.90 (81.0)	26.88 (68.3)	536 (243.1)	F ①	NA	WS-A-3	26-E
112.5	LN3-53345-3S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	800 (362.9)	F	NA	WS-A-4	26-E
150.0	LN3-53346-3S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	950 (430.9)	F	NA	WS-A-4	26-E
225.0	LN3-53347-3S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1256 (569.7)	F	NA	WS-A-4	26-E

① Wall mounting brackets are available for these sizes, refer to page 157.

② 3 KVA through 500 KVA provided with 120V lighting tap limited to 5% of nameplate rating.