



Representative

**Catalog Number:** ASP350  
**Product ID:** 7TAH007890R1139  
**UPC Number:** 78378661071  
**Status:** Active

Type ASP Aluminum Splice, Max 35kV, Wire Size 350 kcmil, Length 3-7/8 Inch, Tin Plated, Die Color Code Brown

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Aluminum Splice
Special Features	Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Material	Aluminum
Finish	Tin Plated
Color	Brown
Voltage Rating	35KV

### European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Material	Other
Surface protection	Tinned
Insulation	None
Voltage row	Up to 35kV

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	4.1x3x2.7
Outer Quantity	20
Outer Dimensions (inches)	14.7x6.5x4.6
Weight Uom	25.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com