

**HALO LED H4 Series 2nd Generation**

The Halo H4 LED is a family of 4" aperture recessed downlight H457 series of housings designed for exclusive use with Halo EL406, ELG406, ELSG406 Series LED Light Engines and compatible 4" TL4 and TLS4 LED trims. Halo H4 LED housings have integral LED drivers that offer dimming as a standard feature.

This is a Non-IC, AIR-TITE™ remodel housing designed for non-insulated ceiling installations, universal voltage 120V-277V input, and dimming with either 120V phase control dimmers, or 0-10V DC control systems. The H4 LED series offers high quality downlighting along with high efficacy – the result being great lighting and significant energy savings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

**DESIGN FEATURES**

**MECHANICAL**

**(A) Housings**

Single wall aluminum housing. Openings are gasketed for AIR-TITE installation. 5 1/2" height allows use in 2"x 6 joist construction. AIR-TITE aperture gasket is pre-installed.

**(B) Remodel Arm**

- Spring steel construction designed for ease of installation and ceiling support of LED driver.

**MOUNTING**

**(C) Remodel Springs**

- Four remodel clips secure housing and accommodate 1/2" and 5/8" ceiling material.

**ELECTRICAL**

**(D) Junction Box**

- Seven 1/2" trade size conduit knockouts with true pry-out slots
- Slide-N-Side™ connectors allow non metallic sheathed cable to be installed without tools and without removing knockouts.
- Accepts a wide range of non-metallic sheathed cables
  - The standard cable types used in lighting in both U.S. and Canada.
  - Allows wiring connections to be made outside the junction box.
  - Simply insert the cable directly into the trap after connections are made.
  - Accommodates the following standard nonmetallic sheathed cable types:  
US: #14/2, #14/3, #12/2, #12/3  
Canada: #14/2, #14/3, #12/2

**LED Connection**

- LED connector is non-screw base offering easy plug-in installation with the H4 LED 2nd Generation EL406, ELG406, ELSG406 Series LED Light Engines.

- LED connector meets high- efficacy luminaire requirement for a non-screw base socket, and where required to qualify as a high- efficacy luminaire (California Title-24).

**LED Driver**

- LED dimmable driver mounts to the housing junction box.
- Driver is a 120V-277V Universal Voltage, high efficiency, electronic power supply providing low voltage power to EL Series LED Light Engines.
- Driver meets FCC EMI/RFI Consumer Level limits for use in residential and commercial installations.
- Driver features high power factor and low THD and has integral thermal protection in the event of over temperature or internal failure.
- Driver is specifically designed for compatibility with EL406 LED Light Engines, and ELG406, ELSG406 Adjustable Gimbal Light Engine / Trims.
- If dimming is not required the fixture can be operated from a standard wall switch

**Dimming - Phase Control**

- The HALO H4 LED luminaire is designed for dimming capability to 10% in normal operation with most 120V leading edge (LE) and trailing edge (TE) phase control dimmers. (Consult dimmer manufacturer for application/ compatibility/loading. Note, some dimmers require a neutral in the wallbox).

**Dimming - 0-10V**

- Dimmable to 10% in typical operation with compatible 0-10V DC low voltage dimmers.
- 0-10V DC dimmers operate using two low voltage dimming wires (color coded violet and gray).

The low voltage dimming wires are separate from the 120V AC or 277V AC power.

- Switching on/off is controlled via the line voltage (120V AC or 277V AC) power, and dimming is controlled via the 2-wire 0-10V DC low voltage wiring.

**Warranty**

Cooper Lighting provides a five year limited warranty on Halo LED Luminaires which includes the LED Recessed Housing, LED Light Engine, and LED trims.

**Labels**

- UL/cUL Listed 1598 Luminaire
- UL/cUL Listed for Damp Location
- UL/cUL Listed for Wet Location, covered ceiling - with select trims

**Qualifications**

- Use with designated LED light engines and trims for ENERGY STAR® qualification.\*\*
- Can be used for State of California Title 24 high efficacy luminaire compliance\*\*
- Can be used for Washington State Energy Code (WSEC) and International Energy Conservation Code (IECC) high efficacy luminaire compliance

**AIR-TITE™**

Certified under ASTM-E283 and listed UL/cUL 1598. May be used to meet restricted air-flow requirements such as:

- Washington State Energy Code (WSEC)
- International Energy Conservation Code (IECC)
- New York State Energy Conservation Construction Code (NY-ECCC)
- State of California Title 24



**H457RTATE010**

**4-Inch LED Recessed Remodel Housing Non-Insulated Ceiling**

**High Efficacy LED Housing – Dimmable**

**FOR USE IN NON-INSULATED CEILINGS**

**CAN BE USED IN INSULATED CEILINGS BUT INSULATION MUST BE KEPT 3" FROM ALL SIDES OF THE HOUSING**


**H4 Series LED Energy Data:**

(Values at non-dimming line voltage.)

Minimum Starting Temp:	-30°C (-22°F)
EMI/RFI:	FCC Title 47 CFR, Part 15, (Consumer)
Sound Rating:	Class A standards
Input Voltage:	120V-277V
Power Factor:	>0.90
Input Frequency:	50/60Hz
THD:	<25%
Input Power:	13W
Input Current:	121mA
Driver Compliance:	UL8750, Class II rated
Maximum Non-IC (Non-Insulated Ceiling) Ambient Continuous Operating Room Temperature:	40°C (104°F)



**DIMENSIONS**



**ORDERING INFORMATION - H4 LED Downlights**

**SAMPLE NUMBER:** H457RTATE010 - EL406927 - TL410SC  
 Complete unit includes LED housing, light engine and trim; ordered separately.

H4 LED Housing			H4 LED Light Engine		
			EL406	CRI	CCT
<b>H457</b> = 4" housing H4 LED series downlight 2nd Generation	<b>RTAT</b> = Remodel Non-Insulated Ceiling, AIR-TITE	<b>E010</b> = LED driver, 120V-277V, 50/60 Hz, dimmable with 120V LE/TE* phase control dimmers and 0-10V DC dimming controls (refer to dimmer manufacturer)	<b>EL406</b> = 4" LED Downlight Engine, 2nd Generation	<b>9</b> = 90 CRI	<b>27</b> = 2700K <b>30</b> = 3000K <b>35</b> = 3500K <b>40</b> = 4000K

Trim Options		Accessories
<b>TL410SC</b> = Specular Clear Reflector, Diffuse Polymer Dome Lens, White Ring, Shower Rated	<b>TL402TBZS</b> = Tuscan Bronze Reflector, Solite® Glass Lens, and Tuscan Bronze Ring, Shower Rated	<b>Thin Profile Designer Trim Rings</b> For use with Round TL4 trims (not compatible with Square TLS4 trims, or adjustable gimballs ELG, ELSG trims.) <b>TRM400WH</b> = White <b>TRM400BK</b> = Black <b>TRM400SN</b> = Satin Nickel <b>TRM400TBZ</b> = Tuscan Bronze <b>TRM400PC</b> = Polished Chrome
<b>TL410H</b> = Haze Reflector, Diffuse Polymer Dome Lens, White Ring, Shower Rated	<b>TL402SBKS</b> = Specular Black Reflector, Solite® Glass Lens, and White Ring, Shower Rated	
<b>TL410WH</b> = White Reflector, Diffuse Polymer Dome Lens, White Ring, Shower Rated	<b>TL403WBS</b> = White Baffle, Solite® Glass Lens, and White Ring, Shower Rated	
<b>TL410SN</b> = Satin Nickel Reflector, Diffuse Polymer Dome Lens, Satin Nickel Ring, Shower Rated	<b>TL403BBS</b> = Black Baffle, Solite® Glass Lens, and White Ring, Shower Rated	
<b>TL410TBZ</b> = Tuscan Bronze Reflector, Diffuse Polymer Dome Lens, Tuscan Bronze Ring, Shower Rated	<b>TLS408WHWB</b> = Square Baffle Trim, Solite® Glass Lens, White Ring with White Baffle, Shower Rated	
<b>TL410SBK</b> = Specular Black Reflector, Diffuse Polymer Dome Lens, White Ring, Shower Rated	<b>TLS408WHBB</b> = Square Baffle Trim, Solite® Glass Lens, White Ring with Black Baffle, Shower Rated	
<b>TL411WB</b> = White Baffle, Diffuse Polymer Dome Lens, White Ring, Shower Rated	<b>TLS408SNBB</b> = Square Baffle Trim, Solite® Glass Lens, Satin Nickel Ring with Black Baffle, Shower Rated	
<b>TL411BB</b> = Black Baffle, Diffuse Polymer Dome Lens, White Ring, Shower Rated	<b>TLS408TBZBB</b> = Square Baffle Trim, Solite® Glass Lens, Tuscan Bronze Ring with Black Baffle, Shower Rated	
<b>TL402SCS</b> = Specular Clear Reflector, Solite® Glass Lens, and White Ring, Shower Rated	<b>TL409WW</b> = Wall Wash, Semi-Specular Clear Reflector with White Ring, Shower Rated	
<b>TL402HS</b> = Haze Reflector, Solite® Glass Lens, and White Ring, Shower Rated	<b>TL409WHWW</b> = Wall Wash, White Reflector with White Ring, Shower Rated	
<b>TL402WHS</b> = White Reflector, Solite® Glass Lens, and White Ring, Shower Rated	<b>TL422PS</b> = Polymer "Dead Front" White Baffle & Regressed Lens, White Ring, Shower Rated	
<b>TL402SNS</b> = Satin Nickel Reflector, Solite® Glass Lens, and Satin Nickel Ring, Shower Rated		

\* LE = Leading Edge (forward phase control) dimming  
 \* TE = Trailing Edge (reverse phase control) dimming

**ORDERING INFORMATION - H4 LED Adjustable Gimballs**

**SAMPLE NUMBER:** H457RTATE010 - ELG406930WH  
 Complete unit includes LED housing, light engine and trim; ordered separately.

H4 LED Light Engine				Optional Accessory Reflector Kit	Optional Len Media
CRI	CCT	Finish			
<b>ELG406</b> = Round LED Adjustable Gimbal Light Engine - 2nd Generation	<b>9</b> = 90 CRI	<b>27</b> = 2700K <b>30</b> = 3000K <b>35</b> = 3500K <b>40</b> = 4000K	<b>WH</b> = White <b>SN</b> = Satin Nickel <b>TBZ</b> = Tuscan Bronze	(order separately) TL412RK includes: • 25° reflector (one is included with gimbal) • 35° reflector • 50° reflector TL412RK is for use with ELGxx and ELSGxx gimballs only.	(order separately) One lens media may be used in place of clear lens. Optical Lenses • L110 Diffuse Sand Blasted Lens • L111 Soft Focus Textured Lens • L113 Prismatic Lens • L115 Linear Spread Lens  Dichroic Color Films • L114 UV Filter • L120 Red • L121 Amber • L122 Yellow • L123 Green • L124 Daylight • L125 Blue • L127 Cosmetic Color Filters • L130 Yellow

Solite® is a registered trademark of AGC Flat Glass North America